

Half Sized, Same Wised

SE-1201 Pro



Electrocardiograph



SE-1201 Pro

Electrocardiograph

Designed for the convenience of caregivers, the SE-1201 Pro enables easy-going workflows. The device will automatically record ECG once the signals are well sampled, and present a timely reminder when the lead wires are misconnected, or the pacemaker is detected.



Intellectual
Sampling



Pacemaker
Detection



Self-adapt
AC Filter



Serious
Diseases Hint



Reverse
Electrode Hint

Seamless Connectivity




Hospitals
EMR/HIS/PACs



Clinics
GDT-based


DICOM/HL7

GDT



SE-1515 Data Management System







Serious Diseases Notification

A red notification will identify the severe illnesses after the diagnosis.

Pacemaker Analysis

80 kHz sampling rate.
 Auto pacemaker detection.
 Pick up pace signals lowest from $30\mu\text{s}$, $500\mu\text{V}$.
 Independent pacemaker detection channel.




Averaged Template

The device identifies the averaged template's P, Q, S, and T points with the relevant measurement parameters. Doctors can relocate these points manually and recalculate the corresponding parameters.

Gesture Amplification & Measurement

Users can amplify any segment of waveforms and measure it on the screen with gesture operation.



Reports Comparison

Users can compare two reports on the screen to follow a patient's clinical condition.



SE-1201 Pro Electrocardiograph

Global Headquarters:

Edan Instruments, Inc. | 15 Jinhui Road, Pingshan District, Shenzhen
518122 P.R. China | +86.755.26898326 | www.edan.com | info@edan.com

U.S. and Canada inquiries:

EDAN Diagnostics, Inc. | 9918 Via Pasar, San Diego, CA 92126
+1.858.750.3066 | www.edandiagnostics.com | edan-info@edandiagnostics.com

© Edan Instruments, Inc. All rights reserved. Features and specifications are subject to change without prior notice. No reproduction, copy or transmission may be made without written permission.
Not all products or features are available in all countries, contact Edan for local availability.